

ALT22A681DB200

Not for New Design

ALT22, Aluminum, Aluminum Electrolytic, 680 uF, 20%, 200 VDC, -40/+85°C, 10 mm



Click [here](#) for the 3D model.

General Information

Series	ALT22
Dielectric	Aluminum Electrolytic
Description	Solder Tag, Aluminum Electrolytic
RoHS	Yes
Lead	2 Flying Leads Solder Tags
AEC-Q200	No
Typical Component Weight	80 g
Notes	Dimensions D And L Include Slewing.

Dimensions

D	40mm +/-1mm
L	45mm +/-2mm
S	10mm +/-0.1mm
LL	10mm +/-0.5mm

Packaging Specifications

Slewing	Yes
Packaging	Tray

Specifications

Capacitance	680 uF
Tolerance	20%
Voltage DC	200 VDC, 230 VDC (Surge)
Temperature Range	-40/+85°C
Rated Temperature	85°C
Life	26000 Hrs
Leakage Current	816 uA (5min 20°C)

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.