



Click [here](#) for the 3D model.

| Dimensions |                      |
|------------|----------------------|
| L          | 7.62mm MAX           |
| H          | 9.14mm MAX           |
| T          | 5.08mm MAX           |
| S          | 5.08mm +/-0.78mm     |
| LL         | 7mm MIN              |
| F          | 0.51mm +0.1/-0.025mm |

| Packaging Specifications |           |
|--------------------------|-----------|
| Packaging                | Bulk, Bag |
| Packaging Quantity       | 250       |

| General Information |                              |
|---------------------|------------------------------|
| Series              | GoldMax 300 Comm X7R HV      |
| Style               | Radial                       |
| Description         | GoldMax, Commercial Standard |
| RoHS                | Yes                          |
| Termination         | Tin                          |
| Failure Rate        | N/A                          |
| AEC-Q200            | No                           |
| Halogen Free        | Yes                          |

| Specifications   |   |
|--|---|
| Capacitance  | 0.33 uF   |
| Measurement Condition  | 1 kHz 1.0Vrms                                   |
| Capacitance Tolerance  | 10%   |
| Voltage DC   | 630 VDC   |
| Dielectric Withstanding Voltage                                    | 945 VDC   |
| Temperature Range  | -55/+125°C                                      |
| Temperature Coefficient  | X7R   |
| Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC) | 0.15, 1kHz 1.0Vrms                              |
| Dissipation Factor   | 2.5% 1kHz 1.0Vrms                               |
| Aging Rate   | 3% Loss/Decade Hour: Referee Time is 1000 Hours |
| Insulation Resistance  | 303 MOhms                                       |