



General Information

Series	C4H
Dielectric	Metallized Polypropylene
Style	Axial Oval
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Miscellaneous	Polyester Tape & Resin Protection.

Specifications

Capacitance	0.068 uF
Capacitance Tolerance	5%
Voltage DC	3000 VDC
Voltage AC	750 VAC
Temperature Range	-40/+85°C
Rated Temperature	70°C
Dissipation Factor	0.05%
Max dV/dt	1250 V/us
ESR	18.3 mOhms (100kHz)
Ripple Current	9 Amps (100kHz 70C), 85 Amps (Peak)

Dimensions

D	24.5mm NOM
D2	18mm
L	44mm NOM
LL	40mm +/-5mm
F	1mm NOM

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	70