



The measurement position of Lead Spacing (S) and Width (V) is critical in straight lead capacitors.

Click [here](#) for the 3D model.

General Information

| | |
|----------------|---------------------------|
| Series | C900AC SFTY X1-400 Y2-250 |
| Style | Radial Disc |
| RoHS | Yes |
| Termination | Tin |
| Lead | V-Crimp |
| Failure Rate | N/A |
| Qualifications | VDE, ENEC, UL, cUL |
| AEC-Q200 | No |

Specifications

| | |
|-----------------------|----------------------------|
| Capacitance | 22 pF |
| Tolerance | 5% |
| Voltage AC | 400 VAC (X1), 250 VAC (Y2) |
| Temperature Range | -40/+125°C |
| Temp. Coefficient | SL |
| Insulation Resistance | 10 GOhms |
| Safety Class | X1/Y2 |

Dimensions

| | |
|---|-----------------|
| D | 7mm MAX |
| T | 5mm MAX |
| S | 10mm +/-1mm |
| F | 0.55mm +/-0.1mm |

Packaging Specifications

| | |
|--------------------|------|
| Packaging | Ammo |
| Packaging Quantity | 1000 |