



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|--------------------------------------|
| Series | C4AF |
| Dielectric | Metallized Polypropylene |
| Style | Radial |
| Features | Harsh Environmental Conditions |
| RoHS | Yes |
| Lead | 4 Wire Leads |
| Qualifications | AEC-Q200, IEC61071, EN61071, VDE0560 |
| AEC-Q200 | Yes |
| Typical Component Weight | 128.9 g |
| Miscellaneous | Rth = 10 C/W. |

Specifications

| | |
|-----------------------|-----------------------------------|
| Capacitance | 15 uF |
| Tolerance | 10% |
| Voltage DC | 700 VDC |
| Voltage AC | 350 VAC |
| Temperature Range | -55/+105°C |
| Rated Temperature | 85°C |
| Insulation Resistance | 2 GOhms |
| Max dV/dt | 50 V/us |
| ESR | 2.8 mOhms |
| Ripple Current | 271 Amps Irms (MAX), 750 Amps Ipk |
| Inductance | 38 nH (ESL) |

Dimensions

| | |
|----|--------------------|
| L | 57.5mm +0.8/-0.7mm |
| H | 50mm +0.3/-0.7mm |
| T | 35mm +0.5/-0.7mm |
| S | 52.5mm +/-0.4mm |
| S1 | 20.3mm +/-0.4mm |
| LL | 6mm +0/-2mm |
| F | 1.2mm +/-0.05mm |

Packaging Specifications

| | |
|--------------------|-----------|
| Packaging | Bulk, Box |
| Packaging Quantity | 23 |