



General Information

Series	C4H
Dielectric	Metallized Polypropylene
Style	Axial Oval
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Miscellaneous	Polyester Tape & Resin Protection.

Specifications

Capacitance	0.68 uF
Capacitance Tolerance	5%
Voltage DC	1200 VDC
Voltage AC	500 VAC
Temperature Range	-40/+85°C
Rated Temperature	70°C
Dissipation Factor	0.05%
Max dV/dt	270 V/us
ESR	6.6 mOhms (100kHz)
Ripple Current	12 Amps (100kHz 70C), 184 Amps (Peak)

Dimensions

D	24mm NOM
D2	18mm
L	58mm NOM
LL	40mm +/-5mm
F	1.2mm NOM

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	50

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.