



General Information

Series	C4H
Dielectric	Metallized Polypropylene
Style	Axial Oval
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Miscellaneous	Polyester Tape & Resin Protection.

Specifications

Capacitance	0.15 uF
Capacitance Tolerance	5%
Voltage DC	2000 VDC
Voltage AC	630 VAC
Temperature Range	-40/+85°C
Rated Temperature	70°C
Dissipation Factor	0.05%
Max dV/dt	700 V/us
ESR	11.3 mOhms (100kHz)
Ripple Current	9 Amps (100kHz 70C), 105 Amps (Peak)

Dimensions

D	22mm NOM
D2	15.5mm
L	44mm NOM
LL	40mm +/-5mm
F	1mm NOM

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	100

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.