



Click [here](#) for the 3D model.

General Information

Series	C700KJN SFTY X1-440 Y1-250
Style	Radial Disc
RoHS	Yes
Termination	Tin
Lead	Crimped
Failure Rate	N/A
Qualifications	TUV, UL, cUL
AEC-Q200	No
Shelf Life	104 Weeks

Specifications

Capacitance	4,700 pF
Tolerance	20%
Voltage AC	440 VAC (X1), 250 VAC (Y1)
Temperature Range	-40/+125°C
Temp. Coefficient	Y5U
Dissipation Factor	5% 1 kHz 5.0Vrms
Insulation Resistance	10 GOhms
Safety Class	X1/Y1
Dielectric Withstanding Voltage	4000 VAC

Dimensions

D	15mm MAX
T	6mm MAX
S	12.5mm +/-0.1mm
LL	18mm +2mm
F	0.6mm +/-0.1mm
V	2.7mm +/-0.5mm

Packaging Specifications

Packaging	Ammo
Packaging Quantity	750