



Click [here](#) for the 3D model.

General Information

Series	C900AH SFTY X1-400 Y1-400
Style	Radial Disc
RoHS	Yes
Termination	Tin
Lead	V-Crimp
Failure Rate	N/A
Qualifications	VDE, ENEC, UL, cUL
AEC-Q200	No

Dimensions

D	7mm MAX
T	5mm MAX
S	10mm +/-1mm
LL	3.5mm +/-1mm
F	0.55mm +/-0.1mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	500

Specifications

Capacitance	22 pF
Tolerance	5%
Voltage AC	400 VAC (X1), 400 VAC (Y1)
Temperature Range	-40/+125°C
Temp. Coefficient	SL
Insulation Resistance	10 GOhms
Safety Class	X1/Y1