



Click [here](#) for the 3D model.

General Information	
Series	C900AC SFTY X1-400 Y2-250
Style	Radial Disc
RoHS	Yes
Termination	Tin
Lead	Crimped Out
Failure Rate	N/A
Qualifications	VDE, ENEC, UL, cUL
AEC-Q200	No

Specifications	
Capacitance	62 pF
Tolerance	5%
Voltage AC	400 VAC (X1), 250 VAC (Y2)
Temperature Range	-40/+125°C
Temp. Coefficient	SL
Insulation Resistance	10 GOhms
Safety Class	X1/Y2

Dimensions	
D	8mm MAX
T	5mm MAX
S	5mm +/-0.8mm
F	0.55mm +/-0.1mm

Packaging Specifications	
Packaging	Ammo
Packaging Quantity	1000