



Click [here](#) for the 3D model.

General Information

| | |
|----------------|---------------------------|
| Series | C900AC SFTY X1-440 Y2-300 |
| Style | Radial Disc |
| RoHS | Yes |
| Termination | Tin |
| Lead | V-Crimp |
| Failure Rate | N/A |
| Qualifications | VDE, ENEC, UL, cUL |
| AEC-Q200 | No |

Dimensions

| | |
|----|-----------------|
| D | 11mm MAX |
| T | 5mm MAX |
| S | 7.5mm +/-1mm |
| LL | 4mm +/-1mm |
| F | 0.55mm +/-0.1mm |

Packaging Specifications

| | |
|--------------------|-----------|
| Packaging | Bulk, Bag |
| Packaging Quantity | 500 |

Specifications

| | |
|-----------------------|----------------------------|
| Capacitance | 4,700 pF |
| Tolerance | 20% |
| Voltage AC | 440 VAC (X1), 300 VAC (Y2) |
| Temperature Range | -40/+125°C |
| Temp. Coefficient | Y5V |
| Dissipation Factor | 5% |
| Insulation Resistance | 10 GOhms |
| Safety Class | X1/Y2 |