



Click [here](#) for the 3D model.

General Information

Series	C900AH SFTY X1-400 Y1-400
Style	Radial Disc
RoHS	Yes
Termination	Tin
Lead	Crimped Out
Failure Rate	N/A
Qualifications	VDE, ENEC, UL, cUL
AEC-Q200	No

Dimensions

D	11mm MAX
T	5mm MAX
S	10mm +/-1mm
LL	4mm +/-1mm
F	0.55mm +/-0.1mm

Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	500

Specifications

Capacitance	1,000 pF
Tolerance	10%
Voltage AC	400 VAC (X1), 400 VAC (Y1)
Temperature Range	-40/+125°C
Temp. Coefficient	Y5P
Dissipation Factor	2.5%
Insulation Resistance	10 GOhms
Safety Class	X1/Y1

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.