



Click [here](#) for the 3D model.

| General Information | |
|---------------------|---------------------------|
| Series | C900AC SFTY X1-400 Y2-250 |
| Style | Radial Disc |
| RoHS | Yes |
| Termination | Tin |
| Lead | Crimped Out |
| Failure Rate | N/A |
| Qualifications | VDE, ENEC, UL, cUL |
| AEC-Q200 | No |

| Specifications | |
|-----------------------|----------------------------|
| Capacitance | 4,700 pF |
| Tolerance | 20% |
| Voltage AC | 400 VAC (X1), 250 VAC (Y2) |
| Temperature Range | -40/+125°C |
| Temp. Coefficient | Y5U |
| Dissipation Factor | 2.5% |
| Insulation Resistance | 10 GOhms |
| Safety Class | X1/Y2 |

| Dimensions | |
|------------|----------------|
| D | 13mm MAX |
| T | 5mm MAX |
| S | 7.5mm +/-1mm |
| F | 0.5mm +/-0.1mm |

| Packaging Specifications | |
|--------------------------|------|
| Packaging | Ammo |
| Packaging Quantity | 1000 |