



Click [here](#) for the 3D model.

**General Information**

Series	EDT
Dielectric	Aluminum Electrolytic
Style	SMD Can
Description	Surface Mount, Aluminum Electrolytic
RoHS	Yes
Lead	V-Chip
Qualifications	AEC-Q200
AEC-Q200	Yes

**Dimensions**

D	8mm +/-0.5mm
L	6.2mm +/-0.3mm
W	0.65mm +/-0.1mm
F	0.3mm MAX
A	8.3mm +/-0.2mm
B	8.3mm +/-0.2mm
C	9.5mm MAX
E	3.3mm +/-0.2mm
G	0.35mm +0.15/-0.2mm
P	2.2mm +/-0.2mm

**Specifications**

Capacitance	47 uF
Tolerance	20%
Voltage DC	25 VDC, 32 VDC (Surge)
Temperature Range	-40/+125°C
Rated Temperature	125°C
Life	1000 Hrs
Dissipation Factor	18%
Ripple Current	75 mAmps (120Hz 125C)
High Temperature Solder	Yes
Leakage Current	11.8 uA (2min 20°C)
Impedance Ratio at -25C	2
Impedance Ratio at -40C	3

**Packaging Specifications**

Packaging	T&R
-----------	-----

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.