



Click [here](#) for the 3D model.

| Dimensions |                |
|------------|----------------|
| D          | 22mm +1mm      |
| L          | 30mm +2mm      |
| S          | 10mm +/-0.5mm  |
| LL         | 5.8mm +/-1mm   |
| F          | 1.5mm +/-0.1mm |

| Packaging Specifications |           |
|--------------------------|-----------|
| Packaging                | Bulk, Bag |

| General Information |                                |
|---------------------|--------------------------------|
| Series              | ELH                            |
| Dielectric          | Aluminum Electrolytic          |
| Description         | Snap-In, Aluminum Electrolytic |
| RoHS                | Yes                            |
| Lead                | 2 Pin                          |
| AEC-Q200            | No                             |

| Specifications        |                          |
|-----------------------|--------------------------|
| Capacitance           | 100 uF                   |
| Capacitance Tolerance | 20%                      |
| Voltage DC            | 400 VDC, 450 VDC (Surge) |
| Temperature Range     | -25/+85°C                |
| Rated Temperature     | 85°C                     |
| Life                  | 2000 Hrs                 |
| Dissipation Factor    | 15% 120Hz 20C            |
| ESR                   | 1.9904 Ohms (120Hz 20C)  |
| Ripple Current        | 0.9 Amps (120Hz 85C)     |
| Leakage Current       | 0.8 mA (5min 20°C)       |