



Click [here](#) for the 3D model.

#### General Information

Series	ELH
Dielectric	Aluminum Electrolytic
Style	Snap-In
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
Lead	2 Pin
AEC-Q200	No

#### Dimensions

D	35mm +1mm
L	45mm +2mm
S	10mm +/-0.5mm
LL	5.8mm +/-1mm
F	1.5mm +/-0.1mm

#### Packaging Specifications

Packaging	Bulk, Bag
Packaging Quantity	200

#### Specifications

Capacitance	2200 uF
Capacitance Tolerance	20%
Voltage DC	200 VDC, 250 VDC (Surge)
Temperature Range	-25/+85°C
Rated Temperature	85°C
Life	2000 Hrs
Dissipation Factor	15% 120Hz 20C
ESR	0.0905 Ohms (120Hz 20C)
Ripple Current	4.95 Amps (120Hz 85C)
Leakage Current	3 mA (5min 20°C)