



Click [here](#) for the 3D model.

Dimensions	
D	22mm +1mm
L	35mm +2mm
S	10mm +/-0.5mm
LL	5.8mm +/-1mm
F	1.5mm +/-0.1mm

Packaging Specifications	
Packaging	Bulk, Bag

General Information	
Series	ELG
Dielectric	Aluminum Electrolytic
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
Lead	2 Pin
AEC-Q200	No

Specifications	
Capacitance	2,200 uF
Capacitance Tolerance	20%
Voltage DC	63 VDC, 79 VDC (Surge)
Temperature Range	-40/+105°C
Rated Temperature	105°C
Life	2000 Hrs
Dissipation Factor	25% 120Hz 20C
ESR	0.151 Ohms (120Hz 20C)
Ripple Current	1.7 Amps (120Hz 105C)
Leakage Current	2.8 mA (5min 20°C)
Impedance Ratio at -25C	2
Impedance Ratio at -40C	6