



Click [here](#) for the 3D model.

Dimensions	
D	22mm +1mm
L	20mm +2mm
S	10mm +/-0.5mm
LL	5.8mm +/-1mm
F	1.5mm +/-0.1mm

Packaging Specifications	
Packaging	Bulk, Bag

General Information	
Series	ELG
Dielectric	Aluminum Electrolytic
Description	Snap-In, Aluminum Electrolytic
RoHS	Yes
Lead	2 Pin
AEC-Q200	No

Specifications	
Capacitance	47 uF
Capacitance Tolerance	20%
Voltage DC	400 VDC, 450 VDC (Surge)
Temperature Range	-25/+105°C
Rated Temperature	105°C
Life	2000 Hrs
Dissipation Factor	15% 120Hz 20C
ESR	4.235 Ohms (120Hz 20C)
Ripple Current	0.35 Amps (120Hz 105C)
Leakage Current	0.6 mA (5min 20°C)
Impedance Ratio at -25C	4