



Click [here](#) for the 3D model.

General Information

Series	PFR/F411
Dielectric	Film/Foil Polypropylene
Style	Radial
Features	Pulse
RoHS	Yes
Lead	Wire Leads
Miscellaneous	An Operating Temperature Up To +105C Is Allowed Under Certain Conditions. Please Consult KEMET For Details.

Dimensions

L	7.2mm MAX
H	6mm MAX
T	4.5mm MAX
S	5mm -0.4mm
LL	4mm +1mm
F	0.5mm +/-0.05mm
G	0.5mm NOM

Packaging Specifications

Packaging	Bulk
Packaging Quantity	1000

Specifications

Capacitance	1000 pF
Capacitance Tolerance	2.5%
Voltage DC	100 VDC
Voltage AC	63 VAC
Temperature Range	-55/+100C
Rated Temperature	85°C
Dissipation Factor	0.04% 1kHz, 0.04% 10kHz, 0.05% 100kHz
Insulation Resistance	30000 GOhms
Max dV/dt	1000 V/us
Inductance	6 nH