


SMC16.5155J100C31TR24

Aliases (F125ZS155J100V)

SMC/F125, Film, Metallized PPS, General Purpose, 1.5 uF, 5%, 63 VAC, 100 VDC, 100°C, 6560, 7mm



Note: '()' correspond to the letters used in the product bulletin

Click [here](#) for the 3D model.

Dimensions	
Chip Size	6560
L	16.5mm +/-0.2mm
W	15mm +/-0.2mm
T	7mm +/-0.2mm
F	0.5mm NOM

Packaging Specifications	
Packaging	T&R
Packaging Quantity	500

General Information	
Series	SMC/F125
Dielectric	Metallized PPS
Style	SMD Chip
Features	High Stability
RoHS	Yes
AEC-Q200	No
Typical Component Weight	2.02 g
Shelf Life	104 Weeks
MSL	2

Specifications	
Capacitance	1.5 uF
Capacitance Tolerance	5%
Voltage AC	63 VAC
Voltage DC	100 VDC
Temperature Range	-55/+125°C
Rated Temperature	100°C
Dissipation Factor	0.15% 1kHz, 0.3% 10kHz
Insulation Resistance	3.3333 GOhms
Max dV/dt	3 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.