


SMW7.3473K250K95TR12

Aliases (F126SM473K250V, SMW100HK5470KK95T1)

Obsolete

SMW/F126, Film, Metallized PPS, General Purpose, 0.047 uF, 10%, 250 VDC, 160 VAC, 125°C, 2824, 3.2mm



Note: '()' correspond to the letters used in the product bulletin

General Information

Series	SMW/F126
Dielectric	Metallized PPS
Style	SMD Chip
Features	High Stability
RoHS	Yes
AEC-Q200	No

Dimensions

Chip Size	2824
L	7.3mm +/-0.4mm
W	6mm +/-0.4mm
T	3.2mm MAX
F	0.5mm NOM

Packaging Specifications

Packaging	T&R
Packaging Quantity	2300

Specifications

Capacitance	0.047 uF
Capacitance Tolerance	10%
Voltage DC	250 VDC
Voltage AC	160 VAC
Temperature Range	-55/ +125°C
Rated Temperature	125°C
Dissipation Factor	0.15% 1kHz, 0.25% 10kHz, 0.5% 100kHz
Insulation Resistance	30 GOhms
Max dV/dt	15 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.