


MMK15155K63B04L16.5TR18

Aliases (F601BD155K063L, MMK15155K63B04L16,5TR18)

Not for New Design

Recommended Replacement Series R60

MMK/F601, Film, Metallized Polyester, General Purpose, 1.5 uF, 10%, 63 VDC, 85°C, 15 mm



Click [here](#) for the 3D model.

General Information	
Series	MMK/F601
Dielectric	Metallized Polyester
Style	Radial
Features	DC Multipurpose Applications
RoHS	Yes
Termination	Tinned Wire
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	1.576 g
Notes	Not for new design – the replacement series is: R60.

Dimensions	
L	18mm MAX
H	10.5mm MAX
T	5.5mm MAX
S	15mm +0.6/-0.1mm
H0	16mm NOM
F	0.8mm NOM

Packaging Specifications	
Packaging	T&R
Packaging Quantity	600

Specifications	
Capacitance	1.5 uF
Tolerance	10%
Voltage DC	63 VDC, 48.8 VDC (100C)
Voltage AC	40 VAC
Temperature Range	-55/+100°C
Rated Temperature	85°C
Dissipation Factor	1% 1kHz
Insulation Resistance	3.3333 GOhms
Max dV/dt	5 V/us
Inductance	6 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute – and we specifically disclaim – any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.