



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|---|
| Series | F461 |
| Dielectric | Metallized Polypropylene |
| Style | Radial |
| Features | MKP, Pulse |
| RoHS | Yes |
| Termination | Cut (Tinned Wire) |
| Lead | Cut/Short |
| AEC-Q200 | No |
| Typical Component Weight | 28.5 g |
| Miscellaneous | The Rated Voltage Decreases 2%/C Between +85C And +105C (1.25%/C For AC). ClimCat: 55/105/56. |
| Notes | Series Replaced by R75. |

Dimensions

| | |
|----|-----------------|
| L | 31.5mm -0.7mm |
| H | 37mm -0.7mm |
| T | 22mm -0.7mm |
| S | 27.5mm +/-0.4mm |
| LL | 4mm +2mm |
| F | 0.8mm +/-0.05mm |
| G | 0.5mm NOM |

Packaging Specifications

| | |
|--------------------|------------|
| Packaging | Pizza, Box |
| Packaging Quantity | 150 |

Specifications

| | |
|-----------------------|-------------------------|
| Capacitance | 5.6 uF |
| Tolerance | 10% |
| Voltage DC | 400 VDC, 240 VDC (105C) |
| Voltage AC | 220 VAC |
| Temperature Range | -55/ +105°C |
| Rated Temperature | 85°C |
| Dissipation Factor | 0.1% 1kHz |
| Insulation Resistance | 5.357 GOhms |
| Max dV/dt | 130 V/us |
| Inductance | 6 nH |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.