


PHE844RD6220MR30L2

Aliases (F844DT224M440ALWOL,
PHE844RD6220MD16R30L2)

PHE844/F844, Film, Metallized Polypropylene, Safety, 0.22 uF, 20%, 440 VAC (X1) (ENEC), 480 VAC (UL, cUL), 1000 VDC, 105°C, 22.5mm



Click [here](#) for the 3D model.

Dimensions	
L	26mm MAX
H	21.5mm MAX
T	11mm MAX
S	22.5mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Packaging Specifications	
Packaging	Tray
Packaging Quantity	253

General Information	
Series	PHE844/F844
Dielectric	Metallized Polypropylene
Style	Radial
Features	EMI Safety
RoHS	Yes
Lead	Wire Leads
Safety Class	X1
Qualifications	ENEC, UL, cUL
AEC-Q200	No
THB Performance	Yes
Typical Component Weight	8.54 g
Miscellaneous	ClimCat: 40/105/56/B.

Specifications	
Capacitance	0.22 uF
Capacitance Tolerance	20%
Voltage AC	440 VAC (X1) (ENEC), 480 VAC (UL, cUL)
Voltage DC	1000 VDC
Temperature Range	-40/+105°C
Rated Temperature	105°C
Dissipation Factor	0.1% 1kHz, 0.4% 10kHz
Insulation Resistance	30 GOhms
Max dV/dt	100 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.