



Click [here](#) for the 3D model.

General Information

Series	F461
Dielectric	Metallized Polypropylene
Style	Radial
Features	MKP, Pulse
RoHS	Yes
Termination	Cut (Tinned Wire)
Lead	Cut/Short
AEC-Q200	No
Typical Component Weight	14 g
Miscellaneous	The Rated Voltage Decreases 2%/C Between +85C And +105C (1.25%/C For AC). ClimCat: 55/105/56.
Notes	Series Replaced by R75.

Dimensions

L	41mm -0.7mm
H	24mm -0.7mm
T	13mm -0.7mm
S	37.5mm +/-0.5mm
LL	4mm +2mm
F	1mm +/-0.05mm
G	0.5mm NOM

Packaging Specifications

Packaging	Pizza, Box
Packaging Quantity	175

Specifications

Capacitance	10 uF
Tolerance	5%
Voltage DC	160 VDC, 96 VDC (105C)
Voltage AC	90 VAC
Temperature Range	-55/ +105°C
Rated Temperature	85°C
Dissipation Factor	0.1% 1kHz
Insulation Resistance	3 GOhms
Max dV/dt	35 V/us
Inductance	6 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.