



Click [here](#) for the 3D model.

Dimensions	
L	41mm -0.7mm
H	44mm -0.7mm
T	24mm -0.7mm
S	37.5mm +/-0.4mm
LL	4mm +2mm
F	1mm +/-0.05mm
G	0.5mm NOM

Packaging Specifications	
Packaging	Pizza, Box
Packaging Quantity	91

General Information	
Series	F611
Dielectric	Metallized Polyester
Style	Radial
Features	MKT (Wound), DC Multipurpose Applications
RoHS	Yes
Lead	Wire Leads
AEC-Q200	No
Typical Component Weight	48 g
Miscellaneous	The Rated Voltage Decreases 1.25%/C Between +85C And +105C (For +125C, Please Consult KEMET). ClimCat: 55/105/56.

Specifications	
Capacitance	100 uF
Capacitance Tolerance	20%
Voltage AC	90 VAC
Voltage DC	160 VDC, 120 VDC (105C)
Temperature Range	-55/+105°C
Rated Temperature	85°C
Dissipation Factor	1.2% 1kHz
Insulation Resistance	100 MOhms
Max dV/dt	3 V/us
Inductance	6 nH

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.