



Click [here](#) for the 3D model.

General Information

| | |
|--------------------------|--------------------------|
| Series | F861 |
| Dielectric | Metallized Polypropylene |
| Style | Radial |
| Features | MKP EMI Safety |
| RoHS | Yes |
| Termination | Tinned Wire |
| Lead | Wire Leads |
| Safety Class | X2 |
| Qualifications | ENEC, UL, cUL, CQC |
| AEC-Q200 | No |
| Typical Component Weight | 2.35 g |
| Miscellaneous | ClimCat: 40/110/56/B. |
| Shelf Life | 104 Weeks |

Specifications

| | |
|-----------------------|--------------|
| Capacitance | 0.022 uF |
| Tolerance | 10% |
| Voltage DC | 630 VDC |
| Voltage AC | 310 VAC (X2) |
| Temperature Range | -40/+110°C |
| Rated Temperature | 110°C |
| Dissipation Factor | 0.3% 1kHz |
| Insulation Resistance | 30 GOhms |
| Max dV/dt | 500 V/us |

Dimensions

| | |
|----|-----------------|
| L | 13mm -0.5mm |
| H | 7.5mm -0.5mm |
| T | 9.5mm -0.5mm |
| S | 10mm +/-0.4mm |
| H0 | 18.5mm +/-0.5mm |
| F | 0.6mm +/-0.05mm |
| G | 0.5mm NOM |

Packaging Specifications

| | |
|--------------------|-----|
| Packaging | T&R |
| Packaging Quantity | 300 |