



Click [here](#) for the 3D model.

General Information

| | |
|----------------|---------------------------------|
| Series | GL-C |
| Style | Inlet |
| Description | Noise Filters |
| Features | Inlet Type |
| RoHS | Yes |
| Qualifications | UL |
| AEC-Q200 | No |
| Miscellaneous | 30 K Self-Temperature Rise Max. |

Dimensions

| | |
|---|----------|
| L | 67mm NOM |
| W | 52mm NOM |
| H | 26mm NOM |

Packaging Specifications

| | |
|--------------------------|------|
| Typical Component Weight | 55 g |
|--------------------------|------|

Specifications

| | |
|-------------------|---|
| Voltage AC | 250 VAC |
| Voltage DC | 250 VDC |
| Voltage | 250 VDC, 1500 VAC Withstanding Voltage 1 Min. Line to Ground |
| Rated Current | 3 A (AC/DC) |
| Ripple Current | 3 A (AC/DC) |
| Temperature Range | -25/+55°C |
| Leakage Current | 0.005 mA |
| ESR | 300 MOhms MIN Insulation 500 VDC 1 Min. Line To Ground |

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.