



Click [here](#) for the 3D model.

#### General Information

Series	HHBC
Style	Through-Hole
Features	Noise Solution, Switching Power Supply Outlets, DC-DC Converter
RoHS	Yes
Miscellaneous	40 (K) Temperature Rise Max.
Core	Fe-Si

#### Specifications

Inductance	67 uH
Inductance Tolerance	20%
Rated Current	8 A
Temperature Range	-40/+125°C
DC Resistance	22.2 mOhms

#### Dimensions

D	33.5mm MAX
L	33.5mm MAX
T	17.1mm MAX
LL	9mm +/-3mm
S	14mm NOM
Wire Size	1.2mm

#### Packaging Specifications

Packaging	Tray
Packaging Quantity	120
Typical Component Weight	37 g

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.