



Click [here](#) for the 3D model.

### General Information

Series	HHBC
Style	Through-Hole
Features	Noise Solution, Switching Power Supply Outlets, DC-DC Converter
RoHS	Yes
Miscellaneous	65 (K) Temperature Rise Max.
Core	Fe-Si

### Specifications

Inductance	219 uH
Inductance Tolerance	20%
Current	15 A
Temperature Range	-40/+125°C
DC Resistance	19.5 mOhms

### Dimensions

D	50.5mm MAX
T	26.5mm MAX
LL	9mm +/-3mm
S	19mm NOM
Wire Size	2mm

### Packaging Specifications

Packaging	Tray
Packaging Quantity	60
Typical Component Weight	149 g