



Click [here](#) for the 3D model.

General Information

Series	HP LDD Indust X7R HT200C
Style	Radial
Description	Commercial, High Temperature
Features	LDD High Temperature 200C
RoHS	No
Prop 65	WARNING: Cancer and reproductive harm - https://www.p65warnings.ca.gov/
Termination	Nickel
Lead	Wire Leads
AEC-Q200	No

Dimensions

L	7.62mm MAX
H	7.62mm MAX
T	3.81mm MAX
S	5.08mm +/-0.762mm
LL	3.175mm MIN
F	0.635mm +0.102/-0.051mm

Packaging Specifications

Packaging	Waffle, Tray
-----------	--------------

Specifications

Capacitance	0.1 uF
Tolerance	10%
Voltage DC	50 VDC
Temperature Range	-55/+200°C
Temp. Coefficient	X7R