



Click [here](#) for the 3D model.

**General Information**

Series	L-RMS
Style	SMD Multi-Layer
Core	Ceramic
Description	Surface Mount Inductor
RoHS	Yes

**Dimensions**

Chip Size	0201
L	0.6mm +/-0.03mm
W	0.3mm +/-0.03mm
T	0.3mm +/-0.03mm

**Packaging Specifications**

Packaging	T&R
Packaging Quantity	15000

**Specifications**

Inductance	0.0043 uH (100 MHz)
Inductance Tolerance	+/-0.3 nH
Inductance	4,300 pH
Temperature Range	-55/+125°C
Current	150 mAmps (MAX)
DC Resistance	400 mOhms
DC Resistance	0.4 Ohms
Self-Resonant Frequency	5700 MHz MIN

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.