



Click [here](#) for the 3D model.

**General Information**

Series	L-PWS
Style	SMD Wire-Wound
Core	Ferrite
Description	Surface Mount Inductor
Features	Standard Type
RoHS	Yes
Notes	Last Order Date June 30, 2023.

**Dimensions**

Chip Size	0805
L	2mm +/-0.2mm
W	1.25mm +/-0.2mm
T	1.25mm +/-0.2mm

**Packaging Specifications**

Packaging	T&R
Packaging Quantity	3000

**Specifications**

Inductance	1 uH (7.96 MHz)
Inductance Tolerance	20%
Inductance	1000 nH
Temperature Range	-40/+105°C
Current	300 mAmps (MAX)
DC Resistance	150 mOhms
DC Resistance	0.15 Ohms
Self-Resonant Frequency	100 MHz

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.