



Click [here](#) for the 3D model.

General Information

Series	L-SMS
Style	SMD Multi-Layer
Core	Ceramic
Description	Shielded, Surface Mount Inductor
Features	Standard Type
RoHS	Yes
Winding Type	Multilayer
Notes	Suggested Replacement - https://www.chilisin.com/en-global/Inductor/Product/BSCL_201212/BSCL002012125R6M00 .

Dimensions

Chip Size	0805
L	2mm +0.3/-0.1mm
W	1.25mm +/-0.2mm
T	1.25mm +/-0.2mm

Packaging Specifications

Packaging	T&R
Packaging Quantity	2000

Specifications

Inductance	5.6 uH (4 MHz)
Inductance Tolerance	20%
Rated Current	15 mAmps (MAX)
Temperature Range	-40/+85°C
DC Resistance	900 mOhms
DC Resistance	0.9 Ohms
Quality Factor	50 at 4 MHz
Self-Resonant Frequency	32 MHz