


L3015C1R0NDWDT

Aliases (L3015C1R0NDWDT)

Obsolete • Scheduled EOL - Last date to buy 30 JUN 2023

KEMET, L-DWD, Ferrite, 30%, 1000 nH, 3015(1212)



Click [here](#) for the 3D model.

Dimensions

Chip Size	3015(1212)
L	3mm +/-0.1mm
W	3mm +/-0.1mm
T	1.5mm MAX

Packaging Specifications

Packaging	T&R
Packaging Quantity	2000

General Information

Series	L-DWD
Style	SMD Wire-Wound
Core	Ferrite
Description	Shielded, Surface Mount Inductor
Features	Low Profile
RoHS	Yes
Notes	Last Order Date June 30, 2023. Suggested Replacement - https://productfinder.pulseelectronics.com/part/BWVF003030151R0T00 .

Specifications

Inductance	1000 nH
Inductance Tolerance	30%
Temperature Range	-25/+120°C
Shielded	true
Current	2100 mAmps (MAX), 2100 mAmps (Self Heating)
DC Resistance	0.03 Ohms
Self-Resonant Frequency	100 MHz MIN

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.