



Click [here](#) for the 3D model.

Dimensions	
L	7.62mm MAX
H	7.62mm MAX
T	3.81mm MAX
S	5.08mm +/-0.762mm
LL	3.175mm MIN
F	0.635mm +0.102/-0.051mm

Packaging Specifications	
Packaging	Waffle, Tray

General Information	
Series	HP LDD Indust X7R HT200C
Style	Radial
Description	Commercial, High Temperature
Features	LDD High Temperature 200C
RoHS	No
Prop 65	⚠ WARNING: Cancer and reproductive harm - http://www.p65warnings.ca.gov .
Termination	Nickel
AEC-Q200	No

Specifications	
Capacitance	0.22 uF
Capacitance Tolerance	10%
Voltage DC	100 VDC
Temperature Range	-55/+200°C
Temperature Coefficient	X7R