


## HT08BN104JN

Aliases (HT08BN104J)

Obsolete

HP LDD Indust COG HT200C, Ceramic, 0.1 uF, 5%, 50 VDC, COG, Commercial, High Temperature, 10.16mm



Click [here](#) for the 3D model.

### Dimensions

L	12.7mm MAX
H	12.7mm MAX
T	6.35mm MAX
S	10.16mm +/-0.762mm
LL	3.175mm MIN
F	0.635mm +0.102/-0.051mm

### Packaging Specifications

Packaging	Waffle, Tray
Packaging Quantity	1

### General Information

Series	HP LDD Indust COG HT200C
Style	Radial
Description	Commercial, High Temperature
Features	LDD High Temperature 200C
RoHS	No
Prop 65	<b>WARNING:</b> Cancer and reproductive harm - <a href="http://www.p65warnings.ca.gov">http://www.p65warnings.ca.gov</a> .
Termination	Nickel
Failure Rate	N/A
AEC-Q200	No

### Specifications

Capacitance	0.1 uF
Capacitance Tolerance	5%
Voltage DC	50 VDC
Dielectric Withstanding Voltage	125 VDC
Temperature Range	-55/+200°C
Temperature Coefficient	COG
Dissipation Factor	0.15%
Insulation Resistance	10 GOhms