



Click [here](#) for the 3D model.

Dimensions

Chip Size	0603
L	1.6mm +/-0.2mm
W	0.8mm +/-0.2mm
T	0.8mm +/-0.2mm
LL	0.4mm +/-0.15mm

Packaging Specifications

Packaging	T&R
Packaging Quantity	3000

General Information

Series	L-DWF
Style	Ferrite
Description	Surface Mount Inductor
Features	Bottom Surface Electrode
RoHS	Yes
Notes	Last Order Date June 30, 2023. Suggested Replacement - https://productfinder.pulseelectronics.com/part/BKPB001608DZ4R7MA2 .

Specifications

Inductance	4700 nH
Inductance Tolerance	20%
Temperature Range	-40/+105°C
Current	145 mAmps (Isat, 30% Drop In Inductance), 470 mAmps (Irms, 40C Rise By Self Heating)
DC Resistance	0.24 Ohms
Self-Resonant Frequency	45 MHz