


L0806BR33JSWST

Aliases (L0806BR33JSWST)

Obsolete

KEMET, L-SWS, SMD Wire-Wound, 330 nH, 5%, 0806



Click [here](#) for the 3D model.

Dimensions	
Chip Size	0806
L	2mm +/-0.2mm
W	1.6mm +/-0.2mm
T	1.6mm +/-0.2mm

Packaging Specifications	
Packaging	T&R
Packaging Quantity	2000

General Information	
Series	L-SWS
Style	Ferrite
RoHS	Yes
Notes	Last Order Date June 30, 2023.

Specifications	
Inductance	330 nH
Inductance Tolerance	5%
Temperature Range	-40/+105°C
Current	490 mAmps (MAX)
DC Resistance	0.21 Ohms
Self-Resonant Frequency	400 MHz MIN

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.