



Click [here](#) for the 3D model.

### Dimensions

Chip Size	1770(6868)
L	17mm +/-0.5mm
W	17.1mm +/-0.5mm
T	7mm MAX
G	11.9mm NOM

### Packaging Specifications

Typical Component Weight	11 g
Packaging	T&R, 330mm
Packaging Quantity	100

### General Information

Series	MPX
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Miscellaneous	40 (K) Temperature Rise Max.

### Specifications

Inductance	2200 nH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	Yes
Current	31 A (Irms, 40C Rise By Self Heating), 25 A (Isat, 20% Drop In Inductance), 34 A (Isat, 30% Drop In Inductance)
DC Resistance	2.6 mOhms
Self-Resonant Frequency	15 MHz