


## L3012C3R3MDWDT

Aliases (L3012C3R3MDWDT)

Obsolete

Scheduled EOL - Last date to buy 30 JUN 2023

KEMET, L-DWD, Ferrite, 20%, 3,300 nH, 3012(1212)



Click [here](#) for the 3D model.

### General Information

Series	L-DWD
Style	SMD Wire-Wound
Core	Ferrite
Description	Shielded, Surface Mount Inductor
Features	Low Profile
RoHS	Yes
Notes	Last Order Date June 30, 2023.

### Dimensions

Chip Size	3012(1212)
L	3mm +/-0.1mm
W	3mm +/-0.1mm
T	1.2mm MAX

### Packaging Specifications

Packaging	T&R
Packaging Quantity	2000

### Specifications

Inductance	3.3 uH (100 kHz)
Inductance Tolerance	20%
Rated Current	910 mAmps (MAX), 1050 mAmps (Self Heating)
Temperature Range	-25/+120°C
Shielded	Yes
DC Resistance	100 mOhms
DC Resistance	0.1 Ohms
Self-Resonant Frequency	55 MHz MIN

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.