



Click [here](#) for the 3D model.

Dimensions	
Chip Size	3015(1212)
L	3mm +/-0.1mm
W	3mm +/-0.1mm
T	1.5mm MAX

Packaging Specifications	
Packaging	T&R
Packaging Quantity	2000

General Information	
Series	L-DWD
Style	Ferrite
Description	Shielded, Surface Mount Inductor
Features	Low Profile
RoHS	Yes
Notes	Last Order Date June 30, 2023. Suggested Replacement - <a href="https://productfinder.pulseelectronics.com/part/BWVF003030152R2M00">https://productfinder.pulseelectronics.com/part/BWVF003030152R2M00</a> .

Specifications	
Inductance	2200 nH
Inductance Tolerance	20%
Temperature Range	-25/+120°C
Shielded	Yes
Current	1480 mAmps (MAX), 1500 mAmps (Self Heating)
DC Resistance	0.058 Ohms
Self-Resonant Frequency	64 MHz MIN