


## L4018C2R2MDWDT

Aliases (L4018C2R2MDWDT)

Obsolete

Scheduled EOL - Last date to buy 30 JUN 2023

KEMET, L-DWD, Ferrite, 20%, 2,200 nH, 4018(1616)



Click [here](#) for the 3D model.

### General Information

Series	L-DWD
Style	SMD Wire-Wound
Core	Ferrite
Description	Shielded, Surface Mount Inductor
Features	Low Profile
RoHS	Yes
Notes	Last Order Date June 30, 2023. Suggested Replacement - <a href="https://productfinder.pulseelectronics.com/part/BWVS004040182R2M00">https://productfinder.pulseelectronics.com/part/BWVS004040182R2M00</a> .

### Dimensions

Chip Size	4018(1616)
L	4mm +/-0.2mm
W	4mm +/-0.2mm
T	1.8mm MAX
S	2.5mm +/-0.2mm

### Packaging Specifications

Packaging	T&R
Packaging Quantity	3500

### Specifications

Inductance	2.2 uH (100 kHz)
Inductance Tolerance	20%
Rated Current	2200 mAmps (MAX)
Temperature Range	-25/+120°C
Shielded	Yes
DC Resistance	42 mOhms
DC Resistance	0.042 Ohms
Self-Resonant Frequency	60 MHz

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.