


**MPXV1D1040LR47**

Aliases (UPI2X11040VR47)

KEMET, MPXV, SMD, 470 nH, 20%, 1040(4340)



Click [here](#) for the 3D model.

Dimensions	
Chip Size	1040(4340)
L	10.8mm +/-0.3mm
W	10mm +/-0.2mm
T	4mm MAX
LL	2mm NOM
G	4.7mm +/-0.3mm

Packaging Specifications	
Typical Component Weight	2.2 g
Packaging	T&R, 330mm
Packaging Quantity	500

General Information	
Series	MPXV
Style	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Core	Composite
Miscellaneous	40 (K) Temperature Rise Max.

Specifications	
Inductance	470 nH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	Yes
Current	26.4 A (Irms, 40C Rise By Self Heating), 29 A (Isat, 20% Drop In Inductance), 42 A (Isat, 30% Drop In Inductance)
DC Resistance	2.4 mOhms
Self-Resonant Frequency	65 MHz

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.