

LDEPF2470KA5N00

Aliases (DEPF2470KA5N00)

LDE, Film, Metallized PEN Stacked, Automotive Grade, 0.047 uF, 10%, 630 VDC, 200 VAC, 125°C, 4030, 3.4mm



Click [here](#) for the 3D model.

Dimensions

Chip Size	4030
L	10.5mm +/-0.4mm
W	7.9mm +/-0.5mm
T	3.4mm MAX
B	0.4mm +0.5/-0.3mm

Packaging Specifications

Packaging	T&R
Packaging Quantity	1500

General Information

Series	LDE
Dielectric	Metallized PEN Stacked
Style	SMD Chip
Features	Automotive Grade
RoHS	Yes
Qualifications	AEC-Q200
AEC-Q200	Yes
Typical Component Weight	0.8 g
Shelf Life	104 Weeks
MSL	2a

Specifications

Capacitance	0.047 uF
Capacitance Tolerance	10%
Voltage DC	630 VDC
Voltage AC	200 VAC
Temperature Range	-55/+125°C
Rated Temperature	125°C
Dissipation Factor	0.8% 1kHz
Insulation Resistance	1 GOhms
Max dV/dt	100 V/us