



Click [here](#) for the 3D model.

Dimensions

D	6mm MIN
H	6.7mm MAX
D2	17.5mm MAX
D3	19mm MAX

Packaging Specifications

Packaging	Tray
Packaging Quantity	1200
Component Weight	2.3 g

General Information

Series	MR
Type	Current
Style	Round - Toroidal
Description	Zero-Phase Current Transformers
Features	High Sensitivity, Compact
Lead	2 Pin
RoHS	Yes
Notes	Measurement Conditions: f=60Hz, R=1000 Ohms, I _o =15 mAmps

Specifications

Temperature Range	-20/+80°C
Voltage DC	12.5 mV MIN (Output)
Current	15 Amps
Resistance	30 Ohms
Miscellaneous	Overinput characteristics (After DC5A input) = 10% MAX.