



Click [here](#) for the 3D model.

Dimensions

D	20mm NOM
L	40.4mm NOM

Packaging Specifications

Component Weight	35
Packaging	Bulk Tray, Box
Packaging Quantity	160

General Information

Style	Bolt-On
Description	Langevin Bolt-On Transducers
RoHS	With Exemptions
SCIP Number	6629125f-50d3-4e75-ae76-25e0bc1955b0
Notes	Straight Construction.

Specifications

Series	NBL
Capacitance	1250 pF
Resonant Frequency	60 kHz
Dynamic Admittance	20msec
Mechanical Q	400 Qm
Allowable Velocity	40 cm/S
Allowable Power	3.7
Temperature Range	-40/+120°C