


MPCH0740LR36E

Aliases (UPIC0740LR36E0)

Not for New Design • Scheduled EOL – Last Date to buy 31 JAN 2024

KEMET, MPCH, SMD, 360 nH, 20%, 0740(2716)



Click [here](#) for the 3D model.

Dimensions	
Chip Size	0740(2716)
L	8mm MAX
W	6.7mm +/-0.3mm
T	4mm MAX
LL	1.5mm NOM
G	2mm +/-0.3mm

Packaging Specifications	
Packaging	T&R, 330mm
Packaging Quantity	1000

General Information	
Series	MPCH
Style	Metal Composite
Description	Shielded, Surface Mount Inductor
Features	Large Current Inductors
RoHS	Yes
Core	Composite
Miscellaneous	40 (K) Temperature Rise Max.
Notes	Last time buy due: 31 Jan 2024.

Specifications	
Inductance	360 nH
Inductance Tolerance	20%
Temperature Range	-40/+125°C
Rated Temperature	120°C
Shielded	Yes
Current	22 A (Isat, 20% Drop In Inductance), 23 A (Irms, 40C Rise By Self Heating)
DC Resistance	1.42 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.