



Click [here](#) for the 3D model.

General Information

Series	MPLCH
Style	SMD Molded
Core	Metal Composite
Description	Surface Mount Inductor
Features	Low Profile Power Inductors
RoHS	Yes
Miscellaneous	40 (K) Temperature Rise Max.

Dimensions

Chip Size	2220
L	5.5mm MAX
W	5mm +/-0.2mm
T	1.2mm MAX
G	2.5mm +/-0.2mm

Packaging Specifications

Packaging	T&R, 380mm
Packaging Quantity	5000

Specifications

Inductance	0.68 uH (0.1MHz)
Inductance Tolerance	20%
Rated Current	5.7 A (Irms, 40C Rise By Self Heating)
Saturation Current	7.4 A (Isat, 30% Drop In Inductance)
Temperature Range	-40/+125°C
Rated Temperature	120°C
Shielded	Yes
Current	7.4 A (Isat, 30% Drop In Inductance), 5.7 A (Irms, 40C Rise By Self Heating)
DC Resistance	27.2 mOhms
DC Resistance	27.2 mOhms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.