



Click [here](#) for the 3D model.

Dimensions	
Chip Size	1264(5350)
L	13.2mm +/-0.4mm
W	12.5mm +/-0.2mm
T	6.4mm MAX
LL	2.2mm NOM
G	4.7mm +/-0.3mm

Packaging Specifications	
Typical Component Weight	5.5 g
Packaging	T&R, 330mm
Packaging Quantity	250

General Information	
Series	MPX
Style	Metal Composite
Description	Surface Mount Inductor
Features	Power Inductors
RoHS	Yes
Core	Composite
Miscellaneous	40 (K) Temperature Rise Max.

Specifications	
Inductance	15 uH
Inductance Tolerance	20%
Temperature Range	-55/+155°C
Shielded	Yes
Current	9.8 A (Irms, 40C Rise By Self Heating), 8 A (Isat, 20% Drop In Inductance), 11.5 A (Isat, 30% Drop In Inductance)
DC Resistance	24.9 mOhms
Self-Resonant Frequency	6.5 MHz

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.